

Clubmax 2000

PRODUCT SPECIFICATION SHEET



Over the years, thousands of Clubmax lasers found their customers all around the world. Clubmax systems have a great reputation and hold their price up well. What we offer today is the 3rd generation of our all-time bestseller that we crafted to perfection. Clubmax lasers are available in the range from 2 to 15W.

The Clubmax series lasers are a radically simple solution for anything from several thousand people raves to the smallest private clubs and cosy venues. Developed with regard to challenging clubbing environments, the design is optimised to allow for long maintenance intervals and to ensure a long life span of the system as a whole.

Clubmax 2000

PRODUCT SPECIFICATION SHEET

SPECIFICATIONS

Source Type:	Semiconductor laser diode Full-colour RGB laser projector
Suitability:	Indoor laser displays [atmospheric, abstract, text, animations]
System control:	ILDA [for Ethernet, ArtNet, DMX see ACCESSORIES section of this page]
Compliant with:	EN 60825-1 [tested by TÜV SÜD], FDA
Weight [kg]:	8.5
Size [WxHxD, mm]:	339 x 168 x 270 [Technical Drawings are in SUPPORT section of this page]
Guaranteed opt. output [mW]:	2000
R G B [mW]:	340 700 1200 [*see note A below]
Wavelengths [nm, ±5nm]:	637 520 445
Beam size [mm]:	5.2 x 4.5
Beam divergence [mrad]:	0.58 [full angle, averaged value, *see note B below]
Modulation [kHz] type:	100 analogue
X-Y scanners:	ScannerMAX 506 Compact 40 Kpps @ 8° [more options in UPGRADES section of this page]
Power requirements [V] Input:	100-230/50-60Hz Neutrik powerCON TRUE1
Max. power consumption [VA]:	340
Operation temperature [°C]:	10-40
Included in the set:	1.5M power lead, 10M ILDA signal cable, E-STOP remote with 10M 3-pin XLR cable, set of 4 safety keys, interlock connector [for the USA only], USB memory stick with the user manual.
HW features:	Power output adjustment for each colour, X & Y axes invert, X & Y size and position, scan-fail safety mode selector, scanning system overload protection.
Laser safety features:	Keyed interlock, emission delay, magnetic interlock, scan-fail safety, fast electromechanical shutter [reaction time <20ms], adjustable aperture masking plate, Emergency STOP system with keyed remote and manual RESTART button.
note A	Due to Advanced Optical Correction technology used in Kvant systems, the real power output of each laser module installed within the system may slightly differ from its specification. This doesn't affect the total guaranteed power output of the system.
note B	The beam divergence total is calculated as an average arithmetic value of all individual colours. The divergence of each colour is calculated as: 1. FWHM of the beam cross-section for round beams, or 2. The arithmetic average of the beam's horizontal and vertical divergence for all rectangular beams.